

**What makes the Sonic-Pro ultrasonic flowmeter stand out from the competition?**

# Everything...

## Configuration -

Displays current configuration settings

Example:

1 = 1 inch nominal pipe size

D = doppler mode

0.00 = transducer separation distance

## Goodness of measurement -

Measurement reliability metrics

## Display -

320 x 240 Pixel QVGA Backlit LCD  
UV resistant

## LED status indicators -

Aids in installation and troubleshooting errors

## Hybrid -

User selectable doppler or transit time operating mode

## Power -

AC or DC power input

## Outputs -

Isolated 4-20 mA output  
0-1000 Hz pulse output  
fully configurable, invertible

## Data logging -

Over 500,000 log events possible with included 32 MB SD card (flash memory)

## Communications

Computer connection via RS-232, RS-485, USB, Ethernet  
Includes user PC software

## Process control -

Three independently configurable 10 amp form C, no/nc relays

**ProSeries™**  
by Blue-White Ind.

visit our website at [www.blue-white.com](http://www.blue-white.com)  
5300 Business Drive, Huntington Beach CA 92649